

## Forced Convection Ovens WF-22G



### General Models

Ideal for high temperature storage with user-friendly design.

WF-G Models is used for all sterilization and drying tasks that do not require high drying rates or special time requirements, ideal for drying applications requiring a gentle airflow

### Operating Features

- From +10°C above room temperature to 260°C .
- Microprocess PID control / Auto-tuning / Calibration.
- Digital timer: 1 min to 59 hr. 59 min, delayed ON / OFF.
- Over temperature limit protection / Door opening alarm.
- Conveniently preset 3 most commonly used temperature settings without auto-tuning.
- Digital LED display (1°C resolution) with touch keypads

### Constructional Features

- Gravity-flow convection with vertical airflow for uniform sample heating.
- Three fold tempered glass viewing window allows for easy monitoring of samples.
- Featuring a pull-down door handle.
- Rounded inner chamber corners for easy cleaning and better air-flowing.
- Stainless-steel interior.
- Two circular adjustable top slide vents help to control inner air vapor circulation. (38mm / 1.5" in dia.)

## Specifications

Model		WF-22G
Chamber Volume (L)		150
Temperature	Range (°C)	Amb. +10~ 260
	Fluctuation at 100°C (°C)	0.8
Dimension (W×D×H)	Interior (mm)	500 × 480 × 625
	Exterior (mm)	660 × 750 × 920
Number of shelves		2ea (Max shelves 14ea)
Weight (kg)		72.5
Heating Power		2000
Order No.		12175K

### WIGGENS GmbH

Gässlesweg 22-24, 75334 Straubenhardt, Germany

Tel.: 0049 7248 4529088

### WIGGENS China

Room 303, Hall C, Office Building M8, No.1 Jiuxianqiao East  
Road, Chaoyang District, Beijing 100015, China

Tel: +86 400-809-2068

Fax: +86 400-809-2068-112

Email: [info@wiggens.com](mailto:info@wiggens.com) [service@wiggens.com](mailto:service@wiggens.com)

Website: [www.wiggens.com](http://www.wiggens.com)